

# N2 PSA Nitrogen Generator System For Sale Household Appliances Industry

### **Basic Information**

Place of Origin: SUZHOU, CHINABrand Name: SUMAIRUI GAS

• Certification: ISO9001, CE, BV, SGS, TUV, ASME,

GOST,NB,NR ETC

Model Number: OSP
Minimum Order Quantity: 1 set
Price: Negotiable

Packaging Details: Exporting wooden case /Film packing

Delivery Time: 30-45 days

Payment Terms:
 L/C, T/T, Western Union, MoneyGram

Supply Ability: 100 sets/months



## **Product Specification**

• Design Code: ASME, CE, ISO9001

• Capacity: 100SCFM

Purity: 99.99%-99.999%
 Pressure: 80-105 Psig
 Material: Mild Steel

• Certificates: CE, ISO, ASME, GOST, KGS, NB Etc

PLC: Siemens S7-1200/1500
 HMI: 7inches/12 Inches
 Flow Meter: Vortex Type/ Metal Rota

Oxygen Analyzer: YesMonometer: 1 Lot

Working Mode: Fully AutomaticType Of N2 Generator: PSA Modular CMS

Working Life: >10 YearsMovable: Customize

#### **Product Description**

#### 100SCFM OSP series nitrogen generator for household appliances Industry with ISO, ASME, CE certificates

Our simple turnkey Pressure Swing Adsorption (PSA) type Nitrogen Generator provides a cost-effective means for on-site N2 gas generation. It is based on using the latest PSA technology and utilizes Carbon Molecular Sieve (CMS) to separate nitrogen from the other gases contained in air. The Nitrogen Generator uses two beds of CMS to separate compressed air into a high-pressure nitrogen product stream and low-pressure oxygen enriched waste stream. Typical feed air pressure is 110 psig/7.6 barg. Typical nitrogen product purity for our systems is 99%. Product flow rate for the same system will be higher with better nitrogen recovery if a higher oxygen content can be accepted in the nitrogen product. Systems are available with a product purity up to 99.999% nitrogen (10 ppmv oxygen).

Generators are supplied as complete systems, ready for hookup to a compressed air supply, including air filters and controls for automatic operation. Start up is at the flip of a switch and maintenance is limited to changing filters every three to twelve months. Each Nitrogen Generator comes pre-tested and fine tuned to meet the customer specified nitrogen flow rate and purity.

Benefits compared to previous models

Higher quality materials Lower energy consumption Shorter lead time Longer N2 generator lifetime

How did we do it

Simplification - 80% less parts used in our production process

Automation - state-of-the-art welding and bending robots

Modular isolation - two standard size PSA pressure vessels for all capacities

Service and maintenance

A smaller power consumption requires a smaller compressor. As a result, you will not only save on energy but also on running/service costs of the compressor. Furthermore, the stainless-steel valves have a longer lifetime than brass.

Item	Nitrogen purity (Nm³/hr)							Dimensions	Weight
	95%	99%	99.5%	99.9%	99.99%	99.995%	99.999%	(L*W*H) mm	KG
OSP5	21	13	11	8	5	4.2	3	1100*600*1700	300
OSP10	38	29	25	15	10	7.5	6.1	1200*650*1800	450
OSP20	80	56	52	32	20	16	14	1600*1000*2200	450
OSP40	160	116	105.2	67.2	40	34	28	1800*1000*2200	600
OSP60	252	174	157.8	100.8	60	51	45	1900*1200*2200	750
OSP80	339.2	232	211	132	80	70	62	2000*1200*2400	980
OSP100	420	290	263	168	100	90	78	2100*1600*2500	1300
OSP150	630	435	394.5	252	150	135	120	2500*1800*2600	1600
OSP200	848	580	526	336	200	180	160	2800*1900*2850	2200
OSP250	1060	725	657.5	420	250	225	200	3100*2000*3200	2600
OSP300	1270	870	780	500	300	260	240	3900*2600*3400	3850
OSP400	1696	1160	1052	672	400	360	320	4500*3250*3600	5000
OSP500	2120	1450	1300	840	500	450	400	4900*3600*3800	6500
OSP600	2540	1740	1578	1000	600	540	480	5300*3600*3900	7800
OSP800	3390	2320	2100	1340	800	720	640	5600*3900*4100	10200
OSP1000	4240	2900	2630	1680	1000	900	800	5800*4000*4500	11800

#### Design reference:

Compressed air inlet pressure 7.5 bar(g)/108 psi(g)

Air quality 1.4.1 according to ISO 8573-1:2010

Nitrogen outlet pressure 6 bar(g)/87psi(g)

Nitrogen quality 1.2.1 according to ISO 8573-1:2010.

Designed working temperature max 50 °C

Dew point at Nitrogen outlet - 40 °C

#### Notes:

OSP nitrogen generator max working pressure 10 bar(g)/145psi(g)

Following request of PSA on-site nitrogen generator will be customized:

Working pressure >10 bar(g)/145 psi(g)

Dew point < - 50 °C

Plug and play

Movable/containerized

Other special requirements as per site conditions





# Suzhou Sumairui Gas System Co.,Ltd.



+8613812659092



dylan@sumairui.com



n2-nitrogengenerator.com

No 161, ZhongfengJie, Suzhou High technology district, Suzhou