

SUZHOU, CHINA

GOST,NB,NR ETC

OSP

1 set

Negotiable

30-45 days

100 sets/months

ISO9001, CE, BV, SGS, TUV, ASME,

Exporting wooden case /Film packing

L/C, T/T, Western Union, MoneyGram

Modular PSA Nitrogen Generator Efficiency High Tungsten Molybdenum 65 Scfm

Basic Information

- Place of Origin:
- Brand Name: SUMAIRUI GAS
- Certification:
- Model Number:
- Minimum Order Quantity:
- Price:
- Packaging Details:
- Delivery Time:
- Payment Terms:
- Supply Ability:



Product Specification

Design Code:	ASME, CE, ISO9001
Capacity:	300SCFM
Purity:	99.99%-99.999%
Pressure:	80-105 Psig
Material:	Mild Steel
Certificates:	CE, ISO, ASME, GOST, KGS, NB Etc
PLC:	Siemens S7-1200/1500
HMI:	7inches/12 Inches
Flow Meter:	Vortex Type/ Metal Rota
• Oxygen Analyzer:	Yes
Monometer:	1 Lot
Working Mode:	Fully Automatic
Type Of N2 Generator:	PSA Modular CMS
Working Life:	>10 Years
Application:	Used For Tungsten Molybdenum Industr

N2 generator for heat treatment Tungsten Molybdenum industry with capacity 65 scfm purity 99.999% 110 psig

Nitrogen generators that are based on membrane and pressure swing adsorption (PSA) technologies are both capable of generating nitrogen gas and use compressed air as a means to feed their systems and produce nitrogen. But when deciding which technology will best serve your business, several issues need to be considered. Pressure Swing Adsorption Generators

A PSA nitrogen generator uses a Carbon Molecular Sieve (CMS) to adsorb oxygen under high pressure while allowing the nitrogen to pass through for collection in a storage unit.

PSA Nitrogen Generator – The Process

With the majority of pressure swing adsorption nitrogen generators, two vessels are packed with carbon molecular sieves (CMS) to adsorb oxygen as compressed air moves through the vessel. As one vessel is adsorbing the second vessel is depressurized, and a small amount of nitrogen flows downward to release the oxygen collected during the adsorption process. The two vessels alternate between the adsorption and desorption processes. The entire process for a PSA generator takes approximately 60 seconds.

PSA Nitrogen Generator Systems

Purity Levels

PSA nitrogen generators can provide higher gas purities than can be accomplished with a membrane nitrogen generator. PSA generators manufactured by On Site Gas Systems offer the ability to achieve a set purity level between 95% and 99.9995%. Reliability

On Site Gas Systems PSA nitrogen generators have only a few moving parts and if properly maintained can last for many years. It is not uncommon for an On Site Gas Systems PSA nitrogen generators to maintain its performance for over twenty years.

Very Little Maintenance

An On Site Gas Systems PSA nitrogen generator requires very little maintenance. With clean, dry feed air most of the annual maintenance is simply changes filter cartridge. Pellets that form the hub of the pressure swing adsorption gas filtering process (Zeolite or CMS) have an extensive lifespan and can last for at least for decades. Consistency

Pressure swing adsorption generators can provide the same high volume of nitrogen for the life of the generator

Features and Benefits

Unlimited flexibility: production capacity can be easily adjusted directly on site by simple module additions without any skilled personnel

Compact dimensions for installations even in small or low ceiling spaces of your production facility

Easy fleet management: all OSP models feature the same components, allowing a limited spare parts management and easy maintenance

Non-corrosive materials such as aluminum and stainless steel, for all process components

Item	Nitrogen purity (Nm3/hr)						Dimensions	Weight	
	95%	99%	99.5%	99.9%	99.99%	99.995%	99.999%	(L*W*H) mm	KG
OSP5	21	13	11	8	5	4.2	3	1100*600*1700	300
OSP10	38	29	25	15	10	7.5	6.1	1200*650*1800	350
OSP20	80	56	52	32	20	16	14	1600*1000*220 0	450
OSP40	160	116	105.2	67.2	40	34	28	1800*1000*220 0	600
OSP60	252	174	157.8	100.8	60	51	45	1900*1200*220 0	750
OSP80	339.2	232	211	132	80	70	62	2000*1200*240 0	980
OSP100	420	290	263	168	100	90	78	2100*1600*250 0	1300
OSP150	630	435	394.5	252	150	135	120	2500*1800*260 0	1600
OSP200	848	580	526	336	200	180	160	2800*1900*285 0	2200
OSP250	1060	725	657.5	420	250	225	200	3100*2000*320 0	2600
OSP300	1270	870	780	500	300	260	240	3900*2600*340 0	3850
OSP400	1696	1160	1052	672	400	360	320	4500*3250*360 0	5000
OSP500	2120	1450	1300	840	500	450	400	4900*3600*380 0	6500
OSP600	2540	1740	1578	1000	600	540	480	5300*3600*390 0	7800
OSP800	3390	2320	2100	1340	800	720	640	5600*3900*410 0	10200
OSP1000	4240	2900	2630	1680	1000	900	800	5800*4000*450 0	11800

Design reference : Compressed air inlet pressure 7.5 bar(g)/108 psi(g) Air quality 1.4.1 according to ISO 8573-1:2010 Nitrogen outlet pressure 6 bar(g)/87psi(g) Nitrogen quality 1.2.1 according to ISO 8573-1:2010. Designed working temperature max 50 °C Dew point at Nitrogen outlet - 40 °C

Notes: OSP nitrogen generator max working pressure 10 bar(g)/145psi(g) Following request of PSA on-site nitrogen generator will be customized : Working pressure >10 bar(g)/145 psi(g) Dew point < - 50 °C Plug and play Movable/containerized Other special requirements as per site conditions



